

SM-410 OXISHOCK

ACTIVATED OXYGEN

SM-410 OXISHOCK Concentrated disinfectant based on Activated Oxygen. Acts quickly, without odors and does not change water chemistry. Ideal for both maintenance and shock.



METHOD OF USE AND DOSAGE:

- Directly add to the spa water with the filter in operation.
- Maintenance: Add 2 caps/m³ of water after using the Spa.
- In case of a temporary use, add 5 caps/m³ once a week.
- Shock: If the water is cloudy, add 4 caps/m³. It is also recommended to add 1 cap/m³ of SM-643 Ultra Clear.
- Keep filtration on during 12 hours.

PHYSICAL PROPERTIES:

- Appearance: White granular solid
- Odour: Odourless
- Active oxygen content: minimum 4.5%
- pH (30 g/L solution): 2.1
- Relative density (20 °C): 2.35
- Melting point: Decomposes before melting
- Solubility in water: 297 – 357 g/L (20 °C)

HAZARDS AND PRECAUTIONARY STATEMENTS:

- May intensify fire; oxidizer. Take any precaution to avoid mixing with combustibles.
- Keep away from heat/sparks/open flames/hot surfaces. — No smoking.
- Harmful if swallowed. Causes severe skin burns and eye damage.
- May cause an allergic skin reaction. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Avoid breathing dust.
- Store in a well-ventilated place. Keep container tightly closed. Keep out of reach of children. Store locked up.
- Do not get in eyes, on skin, or on clothing.
- Wear protective gloves/protective clothing/eye protection/face protection. If exposed or if you feel unwell:
- Call immediately a POISON CENTER or doctor/physician. If medical advice is needed, have product container or label at hand.

PACKAGING:

460 g bottles